



MADE IN THE USA

Product Description:

- Hanger - Door - Standard
- Holds BOWMAN® protection systems
- Hooks over a door with a thickness no greater than 2.44"
- Quartz Beige Powder-Coated Steel

Primary Area for Product Usage:

- Anywhere a door hanger is needed to mount a BOWMAN® dispenser for personal protection equipment



Package Specifications:

- Package Quantity: 12 per case
- 14"W x 12"H x 9"D (35.6 cm x 30.5 cm x 22.9 cm)
- 14.0 lbs (6.4 kg) - approximated

Product Specifications (overall external dimensions):

- 5.50"W x 12.13"H x 2.50"D (14.0 cm x 30.8 cm x 6.4 cm)
- 1.1 lbs (0.5 kg) - approximated

Mounting Specifications:



Related Products (each sold separately):

- MB-601: Door Hanger - Long (shown below)



Proper Hanging Procedure:

- 1) Attach hanger securely - back of hanger must lay flush against surface
- 2) Hang empty dispenser on hanger.
- 3) Load product in dispenser.
- 4) To remove, reverse order of steps.







Installation

Always mount dispensers securely *prior* to loading with product.

- Mount hanger to door before attaching a dispenser.
- Top of hanger **MUST** lay flush with top of door. Door thickness cannot exceed 2.44".

**1**

- Mount empty dispenser on hanger. (PS016-0212 shown below.)
- Load dispenser with product.

**2**

Parts included:

- Door hanger

Tools Required:

- No tools required to assemble dispenser

Care and Construction Powder-Coated Steel

Material Characteristics

Designed for Long-Term, Heavy-Duty Applications

Dispensers and stands made of powder-coated steel are both attractive and functional, providing years of service. Our powder-coated steel dispensers and stands provide long-lasting products that hold up well in tough environments.

Powder-coated steel is ideal for dispensers used in a healthcare or an industrial setting. It is impact resistant and is not effected by extremes in temperature.

Care and Cleaning

The powder-coated finish resists common chemicals and cleaning agents and can be easily wiped clean with soap and water.